

SEM300

Vehicle & Motor Controller

Product Highlights

- 24V Sepex Traction and DC Pump
- Tilt sensor and overload system



TRIONIC vehicle controls

General Features

- Integrated dual Sepex Traction motor and DC Pump motor controller
- Integrated tilt sensor can be configured to limit or prevent selected functions when vehicle is tilted
- Platform overload can be configured for EN280 compliance (requires pressure sensor and height sensor [EZfit])
- Flash memory allows factory configuration to exact vehicle needs
- Inputs from platform joystick & switches (or ground mode emergency switches) control vehicle functions via protected valve & line contactor drivers
- Inputs from various cutout switches can be configured to limit or prevent selected functions depending on vehicle state.
- Dual micro-controller ensures failsafe operation
- Available EZcal hand-held allows access to configuration settings and diagnostics including history log (via RS232)
- CAN bus
- Integral status LED provides (flashing) fault code indication

Optional: Text display module provides end-user status & fault descriptions to minimize down time

Technical Data

Power supply	24V	16 to 33 Vdc	Under and Over voltage shutdown
			Reverse battery protected
Drive motor current	200A		
Pump current	300A		
PWM Frequency	16 Khz		
Integral tilt sensor	+/- 0 to 10°	$\sqrt{(x^2+y^2)}$	
Safe High side ON/OFF outputs	4	3A	Automotive spec. protected drivers
Safe High side Proportional outputs	4	3A	Automotive spec. protected drivers
High side ON/OFF outputs	4	3A	Automotive spec. protected drivers
Indicator ON/OFF outputs	6	1A	Automotive spec. protected drivers
Digital inputs	19	1.25ΚΩ	Low impedance eliminates moisture problems
Analog inputs	7	0-5 Vdc	protected from wiring errors
Water proof	IP65		
Ambient working temperature	-40 to +50°C		Controller must be mounted to vehicle frame to provide heatsink
Overall dimensions	8.12" x 6.11" x 2.7" 206 x 155 x 68 mm		LxWxH

EUROPE Trionic Mobility Systems, SAS AMERICAS PG Trionic, Inc.

ASIA Trionic Shenzhen Ltd.

www.trionicgroup.com


rev.T7 Page 1 of 2



SEM300

Vehicle & Motor Controller

Dimensions



Overall Dimensions 8.12 max" x 6.11 max" x2.7" 206 x 155 x 68 mm

Mounting Instructions

The SEM300 control module requires special installation due to its integral tilt sensor. The module must be mounted perpendicular to the ground, with the connectors at the bottom. To achieve full power capability, the base plate should be bolted to a large metal part of the chassis with 4 of M6 x 17mm (min) Bolts oriented at 0° or 90° to the direction of travel.

EUROPE Trionic Mobility Systems, SAS AMERICAS PG Trionic, Inc.

ASIA Trionic Shenzhen Ltd.